


3M™ Heel Grounder HGC1M-C Quick Clasp Cup Style

The Heel Grounder Quick Clasp Cup Style features a push button clasp that reduces the time and effort needed to attach grounders. Adjust the strap to desired fitting and the strap will retain your preferred adjustment. The soft, elastic nylon strap allows for a more comfortable fit and works with a variety of footwear. This Heel Grounder features a durable two-layer sole that can be repositioned for extended life span, and a 23-inch multi-strand ribbon. Heel Grounders are designed and manufactured for comfort and durability. The grounders are UL listed for safety and tested for electrical performance.



WARNING:

All 3M Shoe Grounding Straps and Assemblies should not be used in areas where the individual may come in contact with electrical circuitry exceeding 250 volts.



Electronics Materials Solutions Division Static Control Products

926 JR Industrial Drive
Sanford, NC 27332-9733
Toll-Free: 866-722-3736
International: 919-718-0000
Email: 3mstaticinfo@mmm.com
www.3Mstatic.com

Please recycle. Printed in USA.
© 3M 2014. All rights reserved.
78-9102-1619-7 JHA

Specifications	Typical Value
Elastic Strap	3/4"
Sole Interior	Non-marking
Sole Exterior	<10 ⁵ ohms
Total Grounder*	1.0 x 10 ⁶ ohms

*Meets the requirements of ANSI/ESD S20.20-2007, EIA 625
*ESD-SP9.2

Part Numbers

HGC1M-C	Quick Clasp Heel Grounder, 1 meg resistor
---------	---

How Heel Grounders Work

Heel grounders eliminate a charge on a person by electrically connecting the person to a grounded surface. A conductive ribbon placed inside the wearer's shoe or sock makes electrical contact with the skin through perspiration. The assembly contains a current-limiting resistor which protects the operator from accidental exposure to electricity. Heel grounders must be worn on both feet to maintain ground contact while walking.

3M is a trademark of 3M Company. All other trademarks are owned by their respective companies.

Important Notice

All statements, technical information, and recommendations related to 3M's products are based on information believed to be reliable, but the accuracy or completeness is not guaranteed. Before using this product, you must evaluate it and determine if it is suitable for your intended application. You assume all risks and liability associated with such use. Any statements related to the product which are not contained in 3M's current publications, or any contrary statements contained on your purchase order shall have no force or effect unless expressly agreed upon, in writing, by an authorized officer of 3M.

Warranty; Limited Remedy; Limited Liability.

This product will be free from defects in material and manufacture for one year from the time of purchase. **3M MAKES NO OTHER WARRANTIES INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE.** If this product is defective within the warranty period stated above, your exclusive remedy shall be, at 3M's option, to replace or repair the 3M product or refund the purchase price of the 3M product. **Except where prohibited by law, 3M will not be liable for any indirect, special, incidental or consequential loss or damage arising from this 3M product, regardless of the legal theory asserted.**