



Roller Rejuvenator Product# 1612

Product Description

Citrus-based solvent designed to clean and revitalize rubber rollers and platens. Improves rubber roller grip and reduces mis-feeds and jams.

Features / Benefits

- Improves roller grip
- Natural citrus-based solvent
- Non-ozone depleting

Usage Instructions

FOR PROFESSIONAL OR INDUSTRIAL USE ONLY. Pour onto wipe and rub onto platen/roller surface and leave for 30-45 seconds before wiping off.

Packaging and Availability

1612-2SQ 2 oz. Liquid

Environmental Policy

Techspray® is committed to developing products to ensure a safer and cleaner environment. We will continue to meet and sustain the regulations of all federal, state and local government agencies.

Resources

Techspray® products are supported by global sales, technical and customer services resources.

For additional technical information on this product or other Techspray® products in the United States, call the technical sales department at 800-858-4043, email tsales@techspray.com or visit our web site at: www.techspray.com.

Important Notice to Purchaser/User: The information in this publication is based on tests that we believe are reliable. The results may vary due to differences in tests type and conditions. We recommend that each user evaluate the product to determine its suitability for the intended application. Conditions of use are outside our control and vary widely. Techspray's only obligation and your only solution is replacement of product that is shown to be defective when you receive it. In no case will Techspray® be liable for any special, incidental, or consequential damages based on breach of warranty, negligence or any other theory.



Typical Product Data and Physical Properties

Physical state:	Liquid
Flash point:	Closed cup: 46.1°C (115°F)
Flammable limits:	Lower: 0.7% Upper: 3.1%
Color:	Clear, to light yellow
Odor:	Fruity [strong]
Boiling/condensation point:	163°C (325.4°F)
Volatility:	30% (w/w)
Shelf life:	5 years unopened



● **North America**
 Techspray®
 8125 Cobb Center Drive
 Kennesaw, GA 30152
 800-858-4043
tsales@techspray.com

● **Europe**
 ITW Contamination Control BV
 Saffierlaan 5, 2132 VZ Hoofddorp
 The Netherlands
 +31 88 1307 400
info@itw-cc.com

● **Countries outside the US**
 Call to locate a distributor in your country

X-ON Electronics

Largest Supplier of Electrical and Electronic Components

Click to view similar products for [Chemicals](#) category:

Click to view products by [Techspray](#) manufacturer:

Other Similar products are found below :

[DP-605NS](#) [3045-QT](#) [3125-9S](#) [3748-Q-58"x8"](#) [FO-25DT](#) [S1009-KIT-A-CS8606](#) [DP100-200ML](#) [1743-2FP](#) [152-KA-NC](#) [826-450G](#) [3789-Q](#)
[9729](#) [9223](#) [9945](#) [7000000275](#) [1601](#) [8330-19G](#) [842AR-15ML](#) [841AR-150ML](#) [842AR-P](#) [843WB-15ML](#) [8462-85ML](#) [4354-1L](#) [838AR-P](#)
[838AR-15ML](#) [419D-P-BK](#) [419D-P-GR](#) [419D-P-WH](#) [8MT-450](#) [8MT-25](#) [832HD-25ML](#) [832FX-450ML](#) [834ATH-375ML](#) [832HD-400ML](#)
[8617-1P](#) [843AR-340G](#) [843ER-800ML](#) [9310-300ML](#) [847-1P](#) [4228-225ML](#) [8800-375ML](#) [8810-375ML](#) [8820-2.55L](#) [419E-340G](#) [842UR-](#)
[12ML](#) [419D-1L](#) [CW3300WHITE](#) [CW2205](#) [10447](#) [4140A-945ML](#)